

VISERA 4K UHD

# 4K CAMERA HEAD CH-S400 Clear Image in Every Condition.



### CH-S400 – CAMERA HEAD

## Sharper Images with Less Noise with the 4K Exmor R<sup>®</sup> CMOS Sensor and Optical-Fiber Transmission

- $\cdot$  High sensitivity compared to normal CMOS sensor
- · Less noise (dual noise-reduction function)
- · No delay (4K high-speed transmission)

#### **Optimal View (Fast and Accurate)**

- One-Touch Auto Focus function always enables surgeons to see the fine details of tissue/texture
- Electronic zoom allows surgeons to observe the fine patterns and structures of tissues in the body in high precision even when enlarged

#### Improved Operability (Ergonomic Design)

- $\cdot$  Small, compact camera head
- $\cdot$  New coupler design





Innovation by Sony & Olympus

#### Specifications

		43.6	39.7	46	122.5
Size	Camera head dimen- sions (unit: mm)		$\supset$		

	Camera head weight	280 g	
	Cable	ø 5.1 mm × 3 m	
Observation	Pickup system	CMOS image sensor	
	Focal length	f = 23.5 mm	
NBI observation mode		Available	
Records of camera head information		Available	
Electronic shutter function		Available	
Electronic zoom function		Available	
Cleaning/ Disinfection/	Cleaning/disinfection	Immersible in disinfectant solution	
Sterilization	Sterilization	ETO/Sterrad	
Classification (electro- medical equipment)	Degree of protection	TYPE BF	
	against electric shock		
	Degree of protection against explosion	The camera head should be kept away from flammable gases	
	againer explosion		

Specifications, design, and accessories are subject to change without any notice or obligation on the part of the manufacturer.



#### OLYMPUS EUROPA SE & CO. KG

Postbox 10 49 08, 20034 Hamburg, Germany Wendenstrasse 14–18, 20097 Hamburg, Germany Phone: +49 40 23773-0, Fax: +49 40 233765 www.olympus-europa.com